




## Product Bulletin

### Zilmet ActivFlo

### Proper Residential Sizing

Aug 8, 2023



- The ZAF034 and ZAF010 perform best in the optimal flow rate range of 1.9-5.9 GPM (water flowing through the Activflo)
- The ZAF010H performs best in the optimal flow rate range of 5.9-15.9 GPM (water flowing through the Activflo)
- The Activflo will perform outside of these flow ranges but not optimally



**Best Practice:**

It is better to **UNDERSIZE** the Activflo than to oversize

**Rule-of-Thumb:** A home with 4 bathrooms will typically use a ZAF034 or ZAF010 (match the thread size to the main water supply pipe size for convenience). A home with more than 4 bathrooms and more than 5 people will be best sized with a ZAF010H.

Call Zilmet USA with any of your Activflo questions.